

GENERAL DESCRIPTION
2247400 Basic 47 Laboratory Hood



DETAILS
FULLY ASSEMBLED. HOOD INTERIOR AND EXTERIOR ARE CONSTRUCTED OF GLACIER WHITE, 16 GAUGE, EPOXY STEEL. HOOD INCLUDES 3/16" THICK CLEAR TEMPERED SAFETY GLASS COUNTERBALANCED SASH AND 10 5/16" OD DUCT COLLAR FOR CONNECTION TO THE EXHAUST SYSTEM. HOOD INCLUDES A REMOVABLE FRONT PANEL, AIR FOIL AND TWO-PIECE ADJUSTABLE BAFFLE. THE RIGHT SIDE FIXTURE PANEL IS FACTORY PREPARED TO ACCEPT UP TO THREE SERVICE FIXTURES, ONE FRONT MOUNTED DUPLEX ELECTRICAL RECEPTACLE, AND ONE SIDE WALL-MOUNTED CUP SINK WITH TURRET. THE HOOD LINER IS FACTORY PREPARED FOR TWO APPARATUS RODS.

DIMENSIONS
47" W X 25" D X 48" H

ELECTRICAL
115 VOLTS, SINGLE PHASE, 60 HZ, 10 AMP
HOOD INCLUDES 100 WATT VAPOR-PROOF INCANDESCENT LIGHT FIXTURE, INTERNAL WIRING AND SWITCHES.

PERFORMANCE
STATIC PRESSURE: .35" @ 100 FPM (720 CFM)
SHIPPING WEIGHT
275 LBS.

NOTES
HOOD REQUIRES A REMOTE BLOWER FOR OPERATION
All accessories and kits are field install.



<p>Labconco Corporation 8811 Prospect Avenue Kansas City, Mo 64132-2696 (800) 821-5525 www.labconco.com</p>		<p>FUME HOODS for:</p>
<p>No. _____</p> <p>Date _____</p>	<p>Date: 12/17/03</p> <p>Drawing # 2247400</p> <p>Drawn By: L. Dalton</p> <p>Checked By: _____</p> <p>Approved By: _____</p> <p>Sheet No. _____</p>	

Project No. _____ Project Title: _____