



Canopy Hoods



Canopy Hood 4799000. Blower and ductwork must be ordered separately.

The Canopy Hood is specifically designed to vent non-toxic materials such as heat, steam and odors from large or bulky apparatus such as ovens, steam baths and autoclaves. The hood may be installed on a wall or suspended from the ceiling for peninsular and corner locations. **For most efficient performance, the hood should be installed no more than 12" above the equipment to be ventilated.** Coupled with a blower and ductwork, the Canopy Hood can operate at a wide range of exhaust rates.

Features:

- Glacier white, dry powder epoxy-coated steel construction.
- Integral baffle.
- Fully assembled.
- Include mounting hardware for installation on wall or suspended from ceiling. **Threaded rod is required for suspension from ceiling.**

Both models require (not included):

- **Remote Blower.** See back pocket.
- **Ductwork.** See back pocket.

Nominal Width	Catalog Number	Shipping Weight lbs./kg
4 Feet	4799000	140/64
6 Feet	7099000	205/93


4' Canopy Hood 4799000

CFM at Static Pressure - Inches H ₂ O						
0.12"	0.19"	0.22"	0.36"	0.39"	0.73"	2.45"
325	450	488	650	675	975	1950


6' Canopy Hood 7099000

CFM at Static Pressure - Inches H ₂ O						
0.17"	0.24"	0.31"	0.45"	0.49"	0.89"	2.50"
425	550	638	825	850	1275	2550

Dimensional Data



SIDE



FRONT

Contact Labconco at **800-821-5525** or **816-333-8811** for blower sizing assistance.