



TOP VIEW

Power Requirements					
Country	Volts*	Amps	Hz	Cat #s	Plug
North America	115	16	60	02	Ⓢ
Japan	100	16	50/60	22	Ⓢ
North America	230	8	50/60	12	Ⓢ
Shuko	230	8	50/60	32	Ⓢ
China/Australia	230	8	50/60	42	Ⓢ
British (UK)	230	8	50/60	52	Ⓢ
India	230	8	50/60	72	Ⓢ
Operational Watts					
490 Watts					

* +/- 10% Nominal Value



FRONT VIEW



SIDE VIEW

GENERAL DESCRIPTION

Model: 31262X0X2
 6' PuriCare Procedure Station Class II, Type A2 Biosafety Cabinet
 12" Sash Opening
Certified Product
 * NSF/ANSI 49 Listed
 * ETL Listed to UL 61010-1
 * CE Mark (230V Models)
 * CAN/CSA 22.2 No. 61010-1
 * ADA Compliant Operation
Exterior Superstructure
 * Double Wall Construction * Epoxy Coated Cold Rolled Steel
 * Color: Optic White
Interior Superstructure
 * Type 304 Stainless Steel * Unitized Construction
 * Removable, Seamless, Dished Work Surface with lift out knobs
 * Magnetic Accessory Area on Right Side Interior
Side Panels
 * Each Side * Removable * Color: Optic White
Air Foil
 * Curved, Type 304 Stainless Steel Grille
 * Integral Armrest
 * Reserve-Air Secondary Airflow Slots
Sash
 * Vertical Travel
 * 1/4" Tempered Safety Glass
 * 10 degree angle
Electrical
 * Energy efficient DC-ECM blower operation
 * Direct drive LED lighting up to 180 Footcandles
 * Outlet:
 * 115V Models:
 * Duplex, 115V / 50/60 Hz / GFCI, one on each side
 * 5 amp max
 * 230V Models:
 * Single-Plex, 230V / 50/60 Hz, one on each side
 * 3 amp max
 * Dampened Self-Closing Flush Splash Cover
Logic Information Center
 * 5" Full Color Touchscreen
 * Filter Life Remaining for HEPA Filter
 * Data Logs and System Traceability
 * Visual and Audible Alarms
 * Data Output via USB Export
Controls
 * Right Corner Post * Solid State
Airflow
 * Nominal inflow velocity of 105 feet per minute
 * Nominal downflow velocity of 50 feet per minute
 * Approximately 70% air recirculation
Filters
 * Supply & exhaust 99.99% efficient HEPA filters @ 0.3 um
 * ISO Class 5 conditions per ISO 14644-1 & 2
 * Washable screen-type prefilter located under work surface to trap dander and particulates to extend HEPA filter life
Optional Packages:
 * Accessory Package:
 * UV Light
 * Vacu-Pass Cord & Cable Port Kit, one on each sidewall
 * Service fixture - Right Side - 1/4 turn control handle
Base Stand Options Available: (Sold separately)
 * Telescoping Base Stand (with or without casters)
 * Universal Hydraulic Base Stand (with or without casters)
 * SoLo Hydraulic Lift Base Stand (with casters)

SCALE: SCALED TO FIT

Biological Safety Cabinets for:



LABCONCO CORPORATION • KANSAS CITY MO USA 64132
 800-821-5525 / 816-333-8811 • labconco.com

No.	Date

Date: _____

Drawing #
31262X0X2

Drawn By: _____

Checked By: _____

Approved By: _____

Sheet No. _____